


Layout diagram leXsolar-NewEnergy Ready-to-go

Item-No.2003

Bestückungsplan leXsolar-NewEnergy Ready-to-go

Art.-Nr.2003



- | | | |
|--|---|--|
| <p>1 1400-19 leXsolar-Wind machine
1400-19 leXsolar-Winderzeuger</p> <p>2 1400-08 LED-module 2mA, red
1400-08 LED-Modul 2mA, rot</p> <p>3 1100-27 Motor module without gear
1100-27 Motormodul ohne Getriebe</p> <p>4 1100-26 Light bulb module
1100-26 Glühlampenmodul</p> <p>5 1100-25 Buzzer module
1100-25 Hupenmodul</p> <p>6 1400-22 Wind turbine module
1400-22 Windturbinenmodul</p> <p>7 1100-02 Solar module 0.5 V, 840 mA
1100-02 Solarmodul 0.5 V, 840 mA</p> | <p>8 1100-07 Solar module 1.5 V, 280 mA
1100-07 Solarmodul 1.5 V, 280 mA</p> <p>9 1100-23 Potentiometer module
1100-23 Potentiometermodul</p> <p>10 1100-31 Solar module 2.5 V, 420 mA
1100-31 Solarmodul 2.5 V, 420 mA</p> <p>11 1100-20 Lighting module
1100-20 Beleuchtungsmodul</p> <p>12 1800-15 Distilled water (100 ml)
1800-15 Destilliertes Wasser (100 ml)</p> <p>13 1100-29 Solar cell cover set
1100-29 Satz mit Abdeckung f. Solarzelle</p> <p>14 1400-21 Wind rotor set (assembled)
1400-21 Windrotoren (montierter Satz)</p> <p>15 L2-06-067 Reversible Fuel cell
L2-06-067 Reversible Brennstoffzelle</p> <p>16 1900-01 Water wheel module
1900-01 Wasserradmodul</p> <p>17 1602-01 leXsolar-Base unit small
1602-01 leXsolar-Grundeinheit Small</p> <p>18 1801-02 Electric model car
1801-02 Elektro-Modellfahrzeug</p> | <p>19 1400-12 leXsolar-Wind rotor set
1400-12 leXsolar-Windrotoren</p> <p>20 1100-28 Color discs - Set 1
1100-28 Farbscheiben - Set 1</p> <p>21 1600-02 Capacitor module 5.0F/5.4V
1600-02 Kondensatormodul 5.0F/5.4V</p> <p>22 9100-05 PowerModule
9100-05 PowerModul</p> <p>23 9100-03 AV-Module
9100-03 AV-Modul</p> <p>24 1100-19 leXsolar-Base unit Large
1100-19 leXsolar-Grundeinheit groß</p> <p>25 2xL2-06-033 Short-circuit plug
2xL2-06-033 Kurzschlussstecker</p> <p>26 L2-06-012/013 Test lead 25 cm. black/red
L2-06-012/013 Messleitung 25 cm. schw./rot
L2-06-014/015 Test lead 50 cm. black/red
L2-06-014/015 Messleitung 50 cm. schw./rot</p> <p>27 1602-02 Hand generator
1602-02 Handgeneratormodul</p> <p>28 L2-02-051 Silicone tube 12 mm
L2-02-051 Silikonschlauch innen 12mm</p> |
|--|---|--|

Version number
Versionsnummer

III-01.24_L3-03-259_23.03.2016